

## 4810 SS

Eye / Face wash wall mounted

STANDARD: IS 10592:2018

Meets ANSI Z358.1

INDUSTRY	IDEAL APPLICATIONS
Food / Steel	Corrosive Environment Battery charging areas
Chemical / Mining	Spraying operations Against Acid /
Pharma	Chemical Spillage Dipping operations
Laboratories	Hazardous substances dispensing areas
Automobile	

### SPECIAL FEATURES

 STAINLESS STEEL/ ANTI CORROSIVE	 HIGH DELUGE ACTION	 EASY OPERATION	 EASY MAINTENANCE	 FIRST AID AIDING EQUIPMENT	 DECONTAMINATION UNIT
--	---	---	---	---	---



### EYE / FACE WASH FOUNTAIN

Eye wash fountain head shall be within 38"- 42"  
(96 cm-106 cm) above floor surface as per standard

### EYE WASH HEAD

Two high-flow sprays, operated at low pressure,  
which washes the eye and face

Anti-dust cover protects the head from  
airborne contaminants and automatically  
opens with water pressure

Distance between two eye wash head is  
140 to 200 mm as per standard

### SUPPLY WATER CONDITION

Supply Water	Drinking / Tepid Water
Operating Pressure	2.1 Kg / cm <sup>2</sup> (30 PSI)
Operating Temp	Ambient

### MATERIAL

Pipe	SS 304 Grade
Fitting	SS 304 Grade

### EYE WASH BOWL

SS 304 metal bowl resistant to damage from most acid,  
alkali and oil

Size of SS Bowl 290 ± 3 mm

### PUSH TO OPEN VALVE

½" BSP SS Ball valve connects units to uninterruptible  
water supply as per requirements

### FEATURES

Water inlet connections of 1/2" NB

Water outlet connection – 1¼" NB

Eye wash discharge rate – 12 lpm. (minimum)

Manually operated valve for hazel free usage

Receptor bowl attached for minimize wastage of water

With foot pedal for hands free operation to supply and  
control water flow through eye wash heads

GI Wall bracket for mounting the shower on the walls

### PACKING

1 set per box

### GROSS WEIGHT

4.100 kg